

DL-24ECB EMERGENCY/NORMAL CALL SWITCH WITH VOLUME CONTROL

INTRODUCTION

The DL-24ECB is an Emergency/Normal Call Switch with Volume Control, designed to be used with the DL-24A and DL-24AEXP, Page Control Units. The DL-24ECB is provided with an "Emergency" call button and a "Normal" call button for connection to customer provided signaling equipment.

The "Emergency" button transposes a single press of the button into the four required closures required to generate an "Emergency" class of service call. The "Normal" call button allows a "Normal" class of service call.

FEATURES

- Designed to fit a single-gang electrical box
- No external power source required
- Red "Emergency" button for emergency call
- Black "Call" button for normal call
- Built-in volume control

CONNECTIONS/SETUP

1. Connect switch inputs from control unit to DL-24ECB as shown in connection diagram.
2. Connect Tip and Ring from control unit to DL-24ECB as shown in connection diagram.
3. Connect DL-24ECB to Tip and Ring of 45 Ohm Talkback Speaker.
4. Press either call button to test loudness of tone at speaker and adjust volume of tone through cut-out on the front of the

DL-24ECB enclosure using a 1/16" flat tip screwdriver.

5. Place DL-24ECB over standard single-gang electrical box and fasten in place using the two screws provided.

TECHNICAL ASSISTANCE

When trouble is reported, verify that power is being supplied to the unit and there are no shorts or grounds on cabling.

Assistance in troubleshooting is available from the factory. When calling, you should have a VOM and a telephone test set available and be calling from the job site. Call (540) 563-2000 and ask for Technical Support or (540) 767-1555 for Clarity 24-hour Faxback System or visit our website at <http://www.clarity-com.com>.

Clarity equipment is not field repairable. Clarity maintains service facilities in Roanoke, VA. Should repairs be necessary, attach a tag to the unit clearly stating company name, address, phone number, contact person and the nature of the problem. Send the unit to:

***Repair and Return Dept.
Clarity
5614 Hollins Road
Roanoke, VA 24019-5056***

LIMITED WARRANTY

Clarity warrants its products to be free from defects in materials and workmanship under conditions of normal use and service for a period of one year from the date of shipment. The obligation under this warranty shall be limited to the replacement, repair or refund of any such defective device within the warranty period, provided that:

1. inspection by Clarity indicates the validity of the claim;
2. the defect is not the result of damage, misuse, or negligence after the original shipment;
3. the product has not been in any way repaired by others and that factory sealed units are unopened (A service charge plus parts and labor will be applied to units defaced or physically damaged);
4. freight charges for the return of products to Clarity are prepaid;
5. all units "out of warranty" are subject to a service charge. The service charge will cover minor repairs (Major repairs will be subject to additional charges for parts and labor).

This warranty is in lieu of and excludes all other warranties expressed or implied, and in no event shall Clarity be liable for any anticipated profits, consequential damages, loss of time or other losses incurred by the buyer in connection with the purchase, operation or use of the product.

This warranty specifically excludes damage incurred in shipment. In the event a product is received in damaged condition, the carrier should be notified immediately. Claims for such damage should be filed with the carrier involved in accordance with the F.O.B. point.

DL-24ECB CONNECTIONS

(Rear of Unit)

